


THIS DOCUMENT AND THE INFORMATION IT CONTAINS ARE PROPERTY OF EFFILUX AND CONFIDENTIAL. THEY SHALL NOT BE REPRODUCED NOR DISCLOSED TO ANY PERSON EXCEPT TO THOSE HAVING A NEED TO KNOW THEM WITHOUT PRIOR WRITTEN CONSENT OF EFFILUX

CE DOCUMENT ET LES INFORMATIONS QU'IL CONTIENT SONT CONFIDENTIELS ET SONT LA PROPRIETE EXCLUSIVE DE EFFILUX. ILS NE DOIVENT ETRE COMMUNIQUEES QU'AUX PERSONNES AYANT A EN CONNAITRE ET NE PEUVENT ETRE REPRODUITS NI DIVULGUES A TOUTE AUTRE PERSONNE SANS AUTORISATION PREALABLE ECRITE PAR EFFILUX

QUICK INSTRUCTION GUIDE



- 1-MOUNT THE 2x EFFM-BAUMER ON THE CAMERA AT THE WANTED WORKING DISTANCE
- 2-MOUNT THE BRACKET ON THE LIGHT

BAUMER VERISENS XC SERIES




2x EFFM-BAUMER

ALSO INCLUDED: 8x M4 WASHERS



CAMERA MOUNTING HOLES
AND WORKING DISTANCE ADJUSTMENT :
4x M4X6 (CHC SCREWS INCLUDED)
4x M4 WASHERS (INCLUDED)

LIGHT MOUNTING HOLES :
RING/SDOME/FD : 4x M4x6 (CHC SCREWS INCLUDED)
FD (D>39) : 4x M4x10 (CHC SCREWS INCLUDED)



PLEASE REFER TO THE SPECIFIC DOCUMENTATION FOR WIRING LAYOUT

CAMERA				1 Rue de Terre Neuve Mini Parc du Verger Bâtiment E 91940 Les Ulis, France	
BAUMER VERISENS XC SERIES					
Designation				Mail: sales@effilux.fr Tel : +33 9 72 52 70 03 www.effilux.com	
EFFM-BAUMER					
Revision /	Date 15/11/2023	Unit : mm	General Tolerances		
Scale 1:1	Size A3	Page 1/1	ISO 2768 - fH-E		